



Omron Automation & Safety

## A22RW-3MAA

Tau Wae:	A22RW-3MAA
Kaihanga / Waitohu:	Omron Automation & Safety
Whakaahuatanga hua	CONFIG SW BODY SELECTOR ILLUM
Ngā Rauemi:	A22RW-3MAA.pdf
RoHS Tūnga	Arataki i te kore utu / RoHS e tika ana ma te whakakorenga
Waehere Stock	4851 pcs stock
Tuhinga mai i	Hong Kong
Te Ara Tuhi	DHL/Fedex/TNT/UPS/EMS

**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o A22RW-3MAA

TAU WAE	A22RW-3MAA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY SELECTOR ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Arataki i te kore utu / RoHS e tika ana ma te whakakorenga
HE RAHINGA KEI TE WĀTEA	4851 pcs
PEPA RARAUNGA	A22RW-3MAA.pdf
MOMO	Maintained, Momentary
RAUPAPA	A22RW
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	22.3mm (Round)
ĒTAHI INGOA	A22RW3MAA
TAUMATA WHAKAARO MOE (MSL)	1 (Unlimited)
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	Lead free by exemption / RoHS compliant by exemption
WHAKAAHUATANGA	Illuminated - Blue
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Selector Illuminated - Blue
MOMO KAIHOKO	Selector
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A22RW

### Ngā tūtohu e hāngai ana

Omron Automation & Safety A22RW-3MAA	A22RW-3MAA Kaiwhiwhi	A22RW-3MAA Kaiwhakarato
A22RW-3MAA Utu	A22RW-3MAA Pikitia	A22RW-3MAA Whakaahua
A22RW-3MAA PDF Datasheet	A22RW-3MAA Download Datasheet	Tuhinga A22RW-3MAA
A22RW-3MAA Stock	Hokona A22RW-3MAA	Hokona Omron Automation & Safety A22RW-3MAA
Omron Automation & Safety A22RW-3MAA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A22RW-3MAA	Omron Automation and Safety A22RW-3MAA	

### Ngā Hua e hāngai ana

<p><b>A22RW-3MG-24A-20</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPST-NO 10A I roto i te taonga: 3347 pcs</p> <p><b>RFQ</b></p>	<p><b>A22RW-3MA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 4018 pcs</p> <p><b>RFQ</b></p>
<p><b>A22RW-3AY24A11</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPST 10A 120V I roto i te taonga: 2933 pcs</p> <p><b>RFQ</b></p>	<p><b>A22RW-3MG-T1-20</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPST-NO 10A I roto i te taonga: 3178 pcs</p> <p><b>RFQ</b></p>
<p><b>A22RW-3MG</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 10948 pcs</p> <p><b>RFQ</b></p>	<p><b>A22RW-3MAG</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 5995 pcs</p> <p><b>RFQ</b></p>
<p><b>A22RW-3MAR</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 5241 pcs</p> <p><b>RFQ</b></p>	<p><b>A22RW-3AY12A20</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPST-NO 10A I roto i te taonga: 4183 pcs</p> <p><b>RFQ</b></p>
<p><b>A22RW-3AY-24A-20</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPST-NO 10A I roto i te taonga: 4472 pcs</p> <p><b>RFQ</b></p>	<p><b>A22RW-3MAY</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY SELECTOR ILLUM I roto i te taonga: 2787 pcs</p> <p><b>RFQ</b></p>
<p><b>A22RW-3AYT111</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPST 10A 120V I roto i te taonga: 6512 pcs</p> <p><b>RFQ</b></p>	<p><b>A22RW-3MA24A20</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: SWITCH SELECT 3POS DPST-NO 10A I roto i te taonga: 6428 pcs</p> <p><b>RFQ</b></p>

