



Omron Automation & Safety

## A30NZ-MGA-TYA

Tau Wae:

A30NZ-MGA-TYA

Kaihanga / Waitohu:

Omron Automation & Safety

Whakaahuatanga hua

CONFIG SW BODY PUSHBUTTON ILLUM

Ngā Rauemi:

A30NZ-MGA-TYA.pdf

Waehere Stock

5842 pcs stock

Tuhinga mai i

Hong Kong

Te Ara Tuhi

DHL/Fedex/TNT/UPS/EMS

**TONO MO TE WHAKAHUA**

Ko te whakaahua he tohu. Tirohia nga korero mo nga taipitopito hua.

### Ngā whakaaturanga o A30NZ-MGA-TYA

TAU WAE	A30NZ-MGA-TYA
KAIHANGA	Omron Automation & Safety
WHAKAAHUATANGA	CONFIG SW BODY PUSHBUTTON ILLUM
WHAKAHAERE TOKO WHAKAHAERE / ROHS TŪNGA	
HE RAHINGA KEI TE WĀTEA	5842 pcs
PEPA RARAUNGA	A30NZ-MGA-TYA.pdf
MOMO	Maintained
RAUPAPA	A30NL
E HIAHIA ANA	Contact Block(s), Illumination Source
PIHANGA WHAKAPAE PAEPAE	30.5mm (Round)
ĒTAHI INGOA	A30NZMGATYA Z8052
WHAKAAHUATANGA	Illuminated - Yellow
WHAKAAHUATANGA TAIPITOPITO	Configurable Switch Body Pushbutton, Round Illuminated - Yellow
MOMO KAIHOKO	Pushbutton, Round
(TĪPAKOHIA TUATAHI, KA WHAKAMAHIA NGĀ TAEKA) RARAUNGA WHAKAMAHIA	Omron, A30NL

### Ngā tūtohu e hāngai ana

Omron Automation & Safety A30NZ-MGA-TYA	A30NZ-MGA-TYA Kaiwhiwhi	A30NZ-MGA-TYA Kaiwhakarato
A30NZ-MGA-TYA Utu	A30NZ-MGA-TYA Pikitia	A30NZ-MGA-TYA Whakaahua
A30NZ-MGA-TYA PDF Datasheet	A30NZ-MGA-TYA Download Datasheet	Tuhinga A30NZ-MGA-TYA
A30NZ-MGA-TYA Stock	Hokona A30NZ-MGA-TYA	Hokona Omron Automation & Safety A30NZ-MGA-TYA
Omron Automation & Safety A30NZ-MGA-TYA	Omron Automation & Safety Kaiwhakarato	Omron Automation & Safety Kaiwhiwhi
Omron Automation & Safety A30NZ-MGA-TYA	Omron Automation and Safety A30NZ-MGA-TYA	

### Ngā Hua e hāngai ana

<p><b>A30NZ-MMA-NAA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 6707 pcs</p> <p><b>RFQ</b></p>	<p><b>A30NZ-MGA-TRA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 6811 pcs</p> <p><b>RFQ</b></p>
<p><b>A30NZ-MGA-TOA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 6368 pcs</p> <p><b>RFQ</b></p>	<p><b>A30NZ-MMA-NGA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 6991 pcs</p> <p><b>RFQ</b></p>
<p><b>A30NZ-MMA-TAA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 5869 pcs</p> <p><b>RFQ</b></p>	<p><b>A30NZ-MGA-TAA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 5500 pcs</p> <p><b>RFQ</b></p>
<p><b>A30NZ-MGA-NYA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 6755 pcs</p> <p><b>RFQ</b></p>	<p><b>A30NZ-MMA-NRA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 5910 pcs</p> <p><b>RFQ</b></p>
<p><b>A30NZ-MGA-TGA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 5696 pcs</p> <p><b>RFQ</b></p>	<p><b>A30NZ-MGA-TWA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 6669 pcs</p> <p><b>RFQ</b></p>
<p><b>A30NZ-MMA-TGA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUTTON ILLUM I roto i te taonga: 6364 pcs</p> <p><b>RFQ</b></p>	<p><b>A30NZ-MMA-NYA</b> Kaihanga: Omron Automation &amp; Safety Whakaahuatanga: CONFIG SW BODY PUSHBUT NON-ILLUM I roto i te taonga: 7542 pcs</p> <p><b>RFQ</b></p>

